


DS100Ultra

Process control on cork granulate

Non-destructive TCA content measurement in cork granulate,
with an integrated GC pulsed discharge detector.



Your benefits:

- TCA detection limit as low as 1 ppt
- 2 samples every 10 minutes
- Easy sample loading
- Database for results storage
- Compact footprint:
850 x 700 x 900 mm (LWH)

Contact us for your automation project at info@nucomat.com Visit our website, linkedin page or Youtube channel.

Contact

www.nucomat.com
info@nucomat.com

